

# HORE In The Canal & Completely In The Canal Models

The hearing solution for a customer who wants to hide the device inside the ear. This is the Horentek CIC/ITC. It can be done with two kind of battery: 10 or 312. and it can be chosen in the plus version with a new generation receiver, with two chamber in order to maximize the quality of sound.



	Mini Mito Basic	Mini Mito 8W2	Mini Mito 8W4	Mini Mito 16W6	Mini Mito 16W8
WDR Channels	1	2	4	6	8
Battery Type	312	312	312	312	312
Program Selector	•	•	•	•	•
Volume Control	-	-	-	-	-
i-Scene	-	-	-	•	•
Noise Reduction	-	-	-	•	•
Programmable Memory	2	4	4	6	6
Data Logging	-	-	-	•	•
Auto Fitting	•	•	•	•	•
Tinnitus Treatment	-	•	•	•	•
Feedback Canceller	•	•	•	•	•
Telecoil	-	-	-	-	-
Acoustic Indicators	•	•	•	•	•
Battery Life [hours]*	260	260	260	250	250

### Performance

OSPL 90 [Peak dB SPL]	127	127	127	127	127
Full-On Gain [dB]	44	44	44	44	44
Harmonic Distortion	<3%	<3%	<3%	<3%	<3%
Battery Consumption [mA/h]*	0.65	0.65	0.65	0.7	0.7

- Unavailable

• Available

\* Battery consumption was estimated according to the IEC 60118-7 a 1000Hz @ 65dB  
Data were obtained from tests conducted in accordance with the IEC 60118-7

### Accessories:

- Open Fitting System
- Ear Dome: OPEN, CLOSED

### Accessories for Programming:

- Programming Cable (Hi-Pro)
- Flex Adaptor

### Software:

Horentek Fitting

### Faceplate Colours



01 Beige

### Shell Colours



01 Beige



02 Red



03 Blue

For more Technical Information visit [www.horentek.it](http://www.horentek.it)